



The Anixter Difference

At Anixter, we are serious about service. That is why we design personalized solutions to meet your business requirements. From a warehouse staff that manages and reduces your inventory investments to our financial offerings that help you minimize your cost of doing business, Anixter is committed to you.

Product Enhancement and Packaging

We provide a variety of services to enhance and tailor products according to your specifications and installation requirements, all designed to reduce your material and labor costs. These include cutting, stripping, dyeing, striping, SpeedPull®, paralleling, twisting, printing and kitting.

Inventory Management

We design programs to help you manage and reduce your inventory investment. We provide just-in-time delivery, Kanban, guaranteed inventory, in-plant store, Ready!SM Deployment Services and Rapid FireSM inventory control.

Engineering and Technical Expertise

We have resources to provide you with wire and cable design engineering, technical training, product, industry and technical specialists, technical literature, application engineering and troubleshooting.

Supply Chain Solutions

At Anixter, we take fundamental distribution a step further by applying supply chain principles and best practices to help take the costs out of our customers' business processes. By bundling our products with our innovative Supply Chain Solutions, we ensure our customers get the right product, the first time.

Financial Services

We provide you with the opportunity to use our financial resources instead of your own. Our service products include buy backs, guaranteed inventory programs, consigned inventories (in-plant store), inventory stock rotations, copper billing programs, consolidated invoicing, credit card ordering and cable audits.

eBusiness Solutions

Anixter can provide you with real-time information on the supply chain. Solutions include Web-based supply chain visibility, eAnixter, electronic ordering and invoicing, business-to-business systems integration and customer performance reporting.

Anixter Proudly Distributes:

3M	GS Metals/Flextray
ADC	Hammond
Adalet-PLM	Hoffman
AIW	Harbour Industries
Allied Telesis	Insultab
Alpha Wire	Lake Electric
AmerCable	Lapp USA
American Connector	Marine Tech
Amphenol	Monroe Cable Company
Andrew	Nexans
APC	PANDUIT
AT&T	Pelco
Axis Communications	Prysmian
Belden	Radix
Berk-Tek	Rockbestos
Bosch	Service Wire
Security Systems	Shawflex
Brady	Siemens
Cisco Systems	Sony
Coleman Cable	Stran Technologies
CommScope	Surprenant
Cooper B-Line	Thermax/CDT
Corning	Thermo Electric
Cabling Systems	Therm-O-Link/Vulkor
Data Guide	Thomas & Betts
FCI-Burndy	Transition Networks
Fluke Networks	Tyco Electronics
General Cable (Brand-Rex)	
Greenlee	

Anixter Main Marine and Shipboard Locations:

1750 E. Parham Road, Richmond, VA 23228 · 1.800.842.0076

190 James Drive East, Suite 140, St. Rose, LA 70087 · 1.800.662.7700

MIL-Spec Shipboard and Aerospace Cables

- MIL-DTL-24643 low smoke
- MIL-DTL-24640 lightweight low smoke
- MIL-C-17 coaxial cables
- MIL-PRF-85045 fiber optic cables (Brand-Rex/General Cable)
- MIL-PRF-49291 blown fiber Blolite® (Brand-Rex/General Cable)
- SAE-AS22759 (M22759)
- NEMA-WC27500 (M27500)
- MIL-DTL-55021
- M16878 and other hook-up wires
- LSZH Ethernet cables (Cat 5e)

Portable and Power Cables

- Types SOOW/SO, SJO, SJ, SJT, ST, STO, shielded SO and others for yard operations
- Types W, G-GC, SHD-GC, MPF-GC
- DLO
- Welding cables
- Siemens crane cables
- Jumper cables 5 to 15 kV
- THOF-500 enhanced
- Shore power cables, connectors and custom assemblies

Rig Cables

- IEEE-45 1998 Type P (UL, USCG, DNV, ABS, Transport Canada)
- 2 kV/600 V single conductor power cable
- 600 V power, control and instrumentation
- Unarmored, armored, and armored and sheathed

Commercial Shipboard Cable

- UL UBZV Listed Type TN
- IEEE-45 1998 Type X, LSX

Belden Wire and Cable

Electronic and Commercial Cables

- Multiconductor and multipair (shielded and unshielded)
- Coaxial cables
- Category 5e low smoke zero halogen

Instrumentation Cables

- UL Listed PLTC
- High-temp Teflon® constructions
- Armored and direct burial
- Thermocouple and thermocouple extension cable
- Fiber optic

Connectors, Tools and Other Accessories

- MIL-C-83522 ST
- MIL-PRF-29504 termini
- MIL-PRF-28876 multichannel
- TFOCA tactical
- Fiber optic connectors
- AA59729 fiber furcation units
- Blolite blown fiber optic accessories
- Termination tools
- Test equipment
- Cable glands
- Terminal tubes
- Compression lugs
- Cable ties

Security Solutions

- Video surveillance
- Access control
- Security consoles
- Sound and paging systems
- Fire and intrusion products
- Low-voltage and fiber cabling
- Accessories

Anixter's Supply Chain Solutions Model

- Evaluate all processes involved with material procurement and deployment
- Determine specific areas to streamline – order entry, material management, delivery, freight, etc.
- Develop a well-defined program to minimize costs while maximizing efficiency and reducing risk
- Scale model to match project scope



About Anixter: anixter.com/aboutus

Legal Statement: anixter.com/legalstatement

12D0046X00 © 2013 Anixter Inc. · 09/13

Anixter Inc. World Headquarters

2301 Patriot Boulevard
Glenview, Illinois 60026
224.521.8000

1.800.ANIXTER | anixter.com

