



The Anixter Difference

Anixter's single-use pulling eye system is a cost-effective alternative to traditional pulling eyes. With the ability to attach pulling eyes prior to shipment, Anixter can reduce cable waste and labor cost. READY!™ Grip minimizes tooling and inventory expenditures and improves contractor efficiency.

Anixter cuts the cable to circuit length and installs and fits the lugs to the cable. The prepped cable is put on reels and shipped to the job site.

Features

- Steel lugs
- Can be used on aluminum and copper
- Disposable lugs and lanyards
- Small pulling head
- Suitable for dry pulls

Benefits

- Lower cost than other methods
- Lower cost of tooling
- No increase to cost of conduit
- Easier to pull multiple legs

Cost-Cutting Solutions: READY!™ To Install



Anixter offers electrical contractors a suite of cost-cutting solutions called READY! To Install. These solutions are designed to:

called READY! To Install. These solutions are designed to:

- Reduce unproductive labor
- Minimize scrap and excess
- Mitigate risk
- Increase financial leverage.



To learn more, visit anixter.com/contractorsolutions

Lug With No Lanyard		Disposable Lugs and Lanyards				
AWG	Anixter Part No.	Anixter Part No.	Anixter Part No.	Anixter Part No.	Anixter Part No.	Anixter Part No.
		11 in. Lanyard	14 in. Lanyard	21 in. Lanyard	28 in. Lanyard	35 in. Lanyard
8	452028	---	---	---	---	---
6	---	452045	---	---	---	---
4	---	452041	---	---	---	---
3	---	452037	---	---	---	---
2	---	452033	---	---	---	---
1	---	452029	---	---	---	---
1/0	---	---	452049	452050	452051	452052
2/0	---	---	453459	453460	453461	453462
3/0	---	---	456523	456524	456525	456526
4/0	---	---	452053	452054	452055	452056
250	---	---	452057	452058	452059	452060
300	---	---	473485	473486	473487	473488
350	---	---	461747	461748	461749	461750
400	---	---	473489	473490	473491	473492
500	---	---	452061	452062	452063	452064
600	---	---	456527	456528	456529	456530
750	---	---	456531	456532	456533	456534
1000	---	---	456535	456536	456537	456538

Specifications for THHN and XHHW Copper Wire										
THHN/XHHW Wire Size	Max Load (lb.)		Min Conductor Diameter (in.)	Max Conductor Diameter (in.)	Minimum Conduit Size (in.)*					Crimper
	One Tool	Five Tools			1 Wire	2 Wires	3 Wires	4 Wires	5 Wires	
8	130	650	0.134	0.146	---	---	---	---	---	12 to 15 Ton Die Crimper
6	210	1050	0.169	0.184	---	---	---	---	---	
4	300	1500	0.213	0.232	---	---	---	---	---	
3	400	2000	0.238	0.260	---	---	---	---	---	
2	500	2500	0.268	0.292	---	---	---	---	---	
1	669	3345	0.299	0.332	---	---	---	---	---	
1/0	844	4220	0.336	0.373	1	1 1/4	1 1/4	1 1/2	2	
2/0	1000	5000	0.376	0.419	1	1 1/4	1 1/2	2	2	
3/0	1250	6250	0.423	0.470	1	1 1/2	1 1/2	2	2 1/2	
4/0	1650	8250	0.475	0.528	1 1/4	1 1/2	2	2	2 1/2	
250	2000	10000	0.520	0.575	1 1/4	2	2	2 1/2	2 1/2	
300	2400	12000	0.570	0.631	1 1/4	2	2	2 1/2	2 1/2	
350	2400	12000	0.616	0.681	2	2 1/2	2 1/2	2 1/2	3	
400	2400	12000	0.659	0.728	1 1/2	2 1/2	2 1/2	2 1/2	3	
500	4000	20000	0.736	0.813	1 1/2	2 1/2	2 1/2	3	3 1/2	
600	4200	21000	0.813	0.893	2	2 1/2	3	3	3 1/2	
750	4300	21500	0.908	0.998	2	3	3	3 1/2	4	
1000	5000	25000	1.060	1.153	2	3	3 1/2	4	4 1/2	

* For use on THHN and XHHW copper wire only. May require special service (such as removing bushing and installing extra guide pulleys) when pulling maximum diameter wires through minimum size conduit.

About Anixter: anixter.com/aboutus
 Legal Statement: anixter.com/legalstatement

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 224.521.8000

13D1550X00 © 2013 Anixter Inc. · 09/13

1.800.ANIXTER | anixter.com

