



## Outperforms industrial labellers costing twice as much.

### Leave any jobsite looking better than you found it.

Rugged, versatile and packed with time-saving features, the DYMO® Rhino™ 5200 meets all ANSI and TIA/EIA-606-A labelling standards. Time is money, and exclusive one-touch “Hot Keys” save you both on every job. Just press one “Hot Key” to automatically size, space and format text for perfect patch panel labels – then press another to print matching cable flags or face plate tabs, without retyping!

It's just as easy to print module and fixed-length labels, horizontal and vertical wire wraps, terminal and 110 blocks and much more. Print Code 39 and Code 128 barcodes. Access 100+ industry symbols, fractions and punctuation marks with a few quick keystrokes. Add the optional quick-charging lithium-ion battery for uninterrupted productivity.



Hard Case Kit  
(see back for details)









### DYMO® | Rhino™ 5200 features:

- 1 Meets all ANSI and TIA/EIA-606-A industry labelling standards
- 2 Exclusive one-touch “Hot Keys” automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications
- 3 Prints Code 39 and Code 128 barcodes on 19 mm-wide labels – ideal for asset management
- 4 Uses DYMO® Industrial labels with chemical-, heat- and UV-resistant materials; also prints directly on heat-shrink tubes and non-adhesive labels
- 5 Large 14-character, two-line backlit display
- 6 100-Label Memory for storing commonly used labels



Up to

**19 mm**

IND	LABEL APPLICATIONS	LABEL COLOUR	24 mm label widths not for use with the Rhino™ 5200				
			6 mm	9 mm	12 mm	19 mm	24 mm
<b>Labels that stick and stay stuck.</b> DYMO® Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labelling to OSHA, ISO and ANSI colour standards or labelling in harsh conditions, DYMO® Industrial labels have you covered. DYMO® Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces.  <b>LEARN MORE:</b> <a href="http://www.dymo.com/industrial">www.dymo.com/industrial</a>		<b>BLACK ON WHITE</b>	–	18443 <i>S0718580</i>	18444 <i>S0718600</i>	18445 <i>S0718620</i>	1805430
		<b>BLACK ON YELLOW</b>	–	–	18432 <i>S0718450</i>	18433 <i>S0718470</i>	1805431
		<b>BLACK ON ORANGE</b>	–	–	18435 <i>S0718490</i>	18436 <i>S0718500</i>	1805427
		<b>BLACK ON GREY</b>	–	–	1805413	1805419	1805425
		<b>WHITE ON RED</b>	–	–	1805416	1805422	1805429
		<b>WHITE ON BLACK</b>	–	1805437	1805435	1805436	1805432
		<b>WHITE ON GREEN</b>	–	–	1805414	1805420	1805426
<b>VINYL</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 5.5 m	<b>WHITE ON BLUE</b>	–	–	1805243	1805417	1805423
		<b>WHITE ON PURPLE</b>	–	–	1805415	1805421	1805428
		<b>WHITE ON BROWN</b>	–	–	1805412	1805418	1805424
<b>PERMANENT POLYESTER</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 5.5 m	<b>BLACK ON WHITE</b>	1805442	18482 <i>S0718240</i>	18483 <i>S0718210</i>	18484 <i>S0718220</i>	1734523 <i>S0773830</i>
		<b>BLACK ON CLEAR</b>	1805440	18508DMO <i>S0718160</i>	622289	622290	1805433
		<b>BLACK ON METALLIC</b>	1805441	18485 <i>S0718170</i>	18486 <i>S0718180</i>	18487 <i>S0718200</i>	1805434
<b>HEAT SHRINK TUBES</b> - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 	Length 1.5 m	<b>BLACK ON WHITE</b>	18051 <i>S0718260</i>	18053 <i>S0718280</i>	18055 <i>S0718300</i>	18057 <i>S0718330</i>	1805443
		<b>BLACK ON YELLOW</b>	18052 <i>S0718270</i>	18054 <i>S0718290</i>	18056 <i>S0718310</i>	18058 <i>S0718340</i>	1805444
<b>FLEXIBLE NYLON</b> - UL Recognized Component to UL969 - RoHS compliant 	Length 3.5 m	<b>BLACK ON WHITE</b>	–	–	18488 <i>S0718100</i>	18489 <i>S0718120</i>	1734524 <i>S0773840</i>
		<b>BLACK ON YELLOW</b>	–	–	18490 <i>S0718080</i>	18491 <i>S0718090</i>	1734525 <i>S0773850</i>
<b>NON-ADHESIVE TAG</b> - RoHS compliant 	Length 5.5 m	<b>BLACK ON WHITE</b>	18111 <i>S0718350</i>	–	18113 <i>S0718380</i>	–	–
<b>SELF-LAMINATING</b> - RoHS compliant 	Length 5.5 m	<b>BLACK ON WHITE</b>	–	–	–	–	1734821 <i>S0773860</i>

**Rhino™ 5200 SINGLE UNIT (BOXED)**

Code: S0841460

**Box includes:**

- Rhino™ 5200 printer
- 19 mm white flexible nylon tape
- Quick reference guide
- User manual on CD-rom

**Product specifications:**

- Runs on optional rechargeable lithium-ion battery pack or 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 900 gr

**Optional accessories:**

- AC adapter Code: S0721430
- Rechargeable lithium-ion battery pack Code: S0895840
- Hard case Code: S0902390

**Rhino™ 5200 HARD CASE KIT**

Code: S0841390

**Hard Case Kit includes:**

- Rhino™ 5200 printer
- User manual on CD-rom
- Quick reference guide
- 19 mm white flexible nylon tape
- 12 mm white vinyl tape
- Rechargeable lithium-ion battery pack
- AC adapter

**Product specifications:**

- Runs on included lithium-ion rechargeable battery pack with AC adapter or optional 6 AA batteries
- 1 year warranty + 1 year extra when registering
- Unit weight: 2500 gr

For more information or to find out your nearest distributor, please visit [www.dymo.com/industrial](http://www.dymo.com/industrial) or call us at +44 (0) 20 7341 5529.



©2011 DYMO®  
 DYMO bvba, Industriepark-Noord 30  
 B9100 Sint-Niklaas, Belgium  
[www.dymo.com/industrial](http://www.dymo.com/industrial)