



Powering and Connecting Your World

NEW PRODUCT ANNOUNCEMENT

Hospital-Grade UV Charging Carts and Cabinet

Charge, Sync, Secure and Sanitize up to 32 Tablets or Chromebooks



UVC sanitization and antimicrobial protection help reduce the presence of germs on mobile devices.

Perfect for:

Medical facilities, classrooms, corporate offices and retail stores.

In addition to charging, syncing and securing mobile devices, Tripp Lite's new hospital-grade charging stations feature ultraviolet (UVC) sanitization and antimicrobial protection to help reduce the presence of germs.

Inside the enclosures, timer-controlled UVC lights disrupt the DNA of microorganisms and prevent them from replicating. Interior and exterior surfaces have a patented antimicrobial powder coating with silver ionic technology. The coating is 99.9% effective in inhibiting the growth of bacteria, viruses, mold and fungi.

Available in AC and USB models, the charging stations provide greater peace of mind, especially for users of shared devices.

Key Benefits

HIGH-SPEED CHARGING

- AC model has a dedicated outlet for each device.
- USB models have USB-A ports that provide up to 2.4A per device.

CHEMICAL-FREE DEVICE SANITIZATION

- Timer-controlled ultraviolet (UVC) germicidal lights sanitize devices in 10 minutes.
- An exterior LED indicates when the doors are closed and the timer can be activated.
- If a door is opened during the timer cycle, the UVC lights shut off automatically for safety.

Note: Avoid skin and eye exposure to UVC light.

COMPREHENSIVE PROTECTION

- Patented antimicrobial powder coating with silver ionic technology is 99.9% effective in inhibiting the growth of bacteria and viruses.
- Key-locking doors deter theft of devices and power adapters; padlock hasp accepts a user-supplied lock.
- Flow-through ventilation helps prevent overheating.

CONVENIENT SYNCING

- USB sync port connects to a host computer for wired syncing (USB models only).
- All models are compatible with wireless syncing.

CLUTTER-REDUCING ORGANIZATION

- Device slots are numbered and have removable wire dividers.
- Cord management routes cables, and toolless access panels conceal clutter.
- Doors open at least 180° for improved access to devices.

CONVENIENT MOBILITY (Carts Only)

- Wide-grip handle assists cart control.
- Swivel casters with large, non-marking wheels improve handling over uneven surfaces. The casters lock to help prevent unwanted movement.
- Input cord wrap keeps cord out of the way.

Feature Focus

A 99.9% Effective Antimicrobial Protection

Interior and exterior surfaces, including the handle on the carts, have a patented antimicrobial coating with EPA-registered and FDA-compliant silver ionic technology.



B UVC Germicidal Lights

Timer-controlled UVC lights help disinfect electronic devices by destroying most microbes without the use of damaging heat, liquids or chemicals.



C Timer Start Button

The touch of a button initiates a 10-minute sanitizing cycle. LEDs indicate when the timer can be started and when the cycle is in progress.




D Key Lock

Steel enclosure locks with the included keys. A padlock hasp provides another security option.



Model: CSC32ACWHG



Model: CS16USBWHG

E Device Slots

Slots are numbered and have removable dividers to accommodate larger devices.



F Toolless Access Panel(s)

Panels conceal cord clutter and are easily removed for access to outlets or USB ports.



G Input Cord Wrap (Carts Only)


The power cord stays out of the way when not in use.

H Swivel Casters (Carts Only)

Casters enable smooth rolling and lock to prevent movement.

I USB Sync Port (USB Models Only)

Connect to a host computer to update devices. USB cable is included.



SPECIFICATIONS



Model	CSC32ACWHG	CSC32USBWHG	CS16USBWHG
Form Factor	AC Cart for 32 Devices	USB Cart for 32 devices	USB Cabinet for 16 Devices
Compatible Devices	Chromebooks, Laptops, Tablets & Smartphones	Tablets & Smartphones	Tablets & Smartphones
Maximum Screen Size⁽¹⁾	≤15 in. (≤38 cm)	≤15 in. (≤38 cm)	≤15 in. (≤38 cm)
Device Slot Size (HxWxD)	10.5 x 1.5 x 15.4 in. (267.1 x 38.2 x 390.5 mm)	10.5 x 1.5 x 15.4 in. (267.1 x 38.2 x 390.5 mm)	10.6 x 1.5 x 15.4 in. (267.1 x 38.2 x 390.5 mm)
Charging Method	32 AC Outlets (NEMA 5-15R)	32 USB-A Ports	16 USB-A Ports
Charging Capacity⁽²⁾	1440W	2.4A per Port	2.4A per Port
Cart Configuration	Included	Included	Add CSHANDLEKIT2
Rear Mounting Holes	—	—	Yes
Sanitizing Method	UVC Light	UVC Light	UVC Light
Sanitizing Cycle Duration	10 minutes	10 minutes	10 minutes
Primary Construction	Steel with Antimicrobial Powder Coating	Steel with Antimicrobial Powder Coating	Steel with Antimicrobial Powder Coating
Security	Key Lock, Optional Padlock	Key Lock, Optional Padlock	Key Lock, Optional Padlock
Wired USB Syncing	—	Yes	Yes
Wireless Syncing	Compatible	Compatible	Compatible
AC Input	120V	120V	120V
Input Frequency	50/60 Hz	50/60 Hz	50/60 Hz
Input Cord/Plug Type	NEMA 5-15P-HG	NEMA 5-15P-HG	C13 to NEMA 5-15P-HG (detachable)
Input Cord Length	10 ft. (3 m)	10 ft. (3 m)	10 ft. (3 m)
Unit Dimensions (HxWxD)	42.3 x 34.8 x 21.6 in. (1075 x 883.9 x 549 mm) with Handle and Casters	36.1 x 34.8 x 21.6 in. (917 x 884.5 x 549 mm) with Handle and Casters	24.3 x 34.8 x 20.2 in. (617 x 884 x 513 mm)
Limited Warranty	2 Years	2 Years	2 Years

Antimicrobial coating meets JIS Z 2801:2000 efficacy requirements. (1) Depends on device dimensions. (2) 1.5A per port during wired syncing (USB models).

Learn more about Tripp Lite's full line of Charging Carts and Cabinets at triplite.com/cs.



Tripp Lite Corporate Headquarters
1111 West 35th Street, Chicago, IL 60609 USA
773.869.1773 | triplite.com

UV light is shown for illustrative purposes. Under normal use, the UVC lamps will not turn on if the doors are open.
© 2020 Tripp Lite. All trademarks are the property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.