



Powering and Connecting Your World

HIGH-PERFORMANCE POWER PROTECTION, BEST-IN-CLASS SIZE

Meet the 10 to 100kW UPS series that combines a full suite of premium 3-phase features with an ultra-compact footprint, all at a competitive cost.



Tripp Lite's S3M SmartOnline® UPS series provides clean, continuous 10 to 100kW / 208V power in critical applications, with the ability to support 480V and 600V environments as well. With the smallest footprint in the market, the S3M UPS provides the same market-leading features on a 10kW UPS that would typically only be available on a premium 100kW model.

How Small is the S3M Series vs the 208V Competition?



S3M20K vs 2 Competitors

S3M60K vs 2 Competitors

S3M100K vs 2 Competitors

[SEE IDEAL S3M APPLICATIONS \(REVERSE\)](#)

S3M 3-PHASE UPS – IDEAL FOR:



SMALL DATA CENTERS & COLOCATION SITES

Save space for revenue-generating equipment while providing the highest uptime with unyielding UPS battery backup. The scalable S3M series helps IT managers in small, 10- to ≤ 20 -rack data centers adapt to fluctuating equipment demands with flexible configuration options.

- Lower utility and cooling costs with ENERGY STAR 2.0-certified, 94% on-line and 98% ECO mode efficiency
- Unity output power factor (1.0) for supporting more equipment
- Parallel for capacity or redundancy up to 6 units
- Low input distortion (THDi <3%) enables 1:1 generator matching
- 480V and 600V applications supported with 16 different UPS + transformer options



SERVER ROOMS, MICRO DATA CENTERS & EDGE COMPUTING

Protect edge-of-network computing with the highly reliable and easy to manage S3M UPS. The compact S3M is an ideal fit in on-premise and remote edge computing spaces for telecommunications, retail, manufacturing, transportation, corporate, healthcare and financial/educational institutions. With user-friendly management tools and award-winning Tripp Lite customer support, the S3M UPS delivers 3-phase power to edge installations where space and staff resources are limited.

- Large 5-inch (12.7 cm) color touchscreen display for easy configuration and diagnostics
- Dual and single AC input capability for additional system reliability, standard
- Backfeed protection, standard
- Pre- and post-sales support from a dedicated team of highly trained application engineers to help customers find the best power solutions for their unique needs
- Network management options including SNMP, MODBUS, Relay I/O and free downloadable PowerAlert software provide peace of mind via real-time notifications on the state of the UPS



CONTAINERIZED & REMOTE EDGE COMPUTING

Protect against the threats remote computing sites face, such as frequent power outages, voltage irregularities and environmental risks. The S3M UPS series combines compact size with premium 3-phase power and smart remote management and alerts. It is ideal for precast concrete or metal remote micro data centers for utilities, government, telecom and oil/gas exploration.

- Environmental sensors monitor temperature, humidity, door access and water leaks
- On-site (EPO) or remote (REPO) Emergency Power Off capabilities let users monitor and control both the UPS and connected PDUs
- Smart battery charger (20-80 amp) for riding through successive power failures
- Up to 75% less time to repair due to innovative design
- 2-year warranty for UPS with and without internal batteries. Extended warranties available

Visit tripplite.com for more information.



Tripp Lite Corporate Headquarters
1111 West 35th Street | Chicago, IL 60609 USA
+1.773.869.1212 | tripplite.com