

VELCRO® brand
Adhesives



PRESSURE SENSITIVE, FIRE RETARDANT, SOLVENT AND HEAT ACTIVATED



VELCRO® brand Adhesives

VELCRO® brand products are available with a variety of adhesives to best fit your application. Before using an adhesive for production, it should be tested to determine the suitability of the product for its intended use. Please note that this guide covers our most popular adhesives - contact us if you have special requirements.

Types of Adhesive Systems

Woven VELCRO® brand tapes have a binder coat which firmly locks hooks and loops in place and helps prevent fraying of the tapes when cut. Due to this coating, many commercially available adhesives will not readily adhere to the back of woven tape. Therefore, the use of a VELCRO® brand pre-coated adhesive backing is recommended.

Pressure Sensitive Adhesives

Pressure sensitive adhesives are popular because of the ease of application. Simply remove the release liner and press the VELCRO® brand tape in place. Pressure sensitive adhesives should always be considered semi-permanent bonds. VELCRO® brand pressure sensitive adhesives have been engineered to offer specific performance characteristics to meet different requirements.

Solvent and Heat Activated Adhesives

Solvent and heat activated adhesives, available on most VELCRO® brand hook and loop tapes, provide the strongest bond to the tape itself and can be made ready for instant bonding by many easy methods of application (e.g. solvent, heat, ultrasonic, dielectric).

Applications



Pressure Sensitive Adhesives

Acrylic

Acrylic pressure sensitive adhesives offer good shear strength, environmental resistance, and have good adhesion to most metal and medium/high surface energy plastics.

VELCRO® brand Adhesive 72

- Formulated for high temperature performance and superior bond strength
- Moderate tack - medium set up
- Full bond strength in 24 hours
- Temperature operating range -20°F to 225°F

VELCRO® brand Adhesive 75

- Formulated for vinyl substrates
- Moderate tack - medium set up
- Full bond strength in 24 hours
- Temperature operating range -20°F to 230°F

Synthetic Rubber

Rubber-based pressure sensitive adhesives have good adhesion to low surface energy substrates. They should be used indoors, at room temperature.

VELCRO® brand Adhesive 13

- Formulated especially for resistance to light moisture
- High tack - quick setting
- Achieves 80% bond strength in an hour; full strength in 24 hours
- Temperature operating range -20°F to 180°F

VELCRO® brand Adhesive 15

- Formulated for many substrates, especially uneven or rough surfaces
- High tack - quick setting
- Achieves 80% bond strength in about an hour; full strength in 30 hours
- Temperature operating range -40°F to 120°F
- Recommended for most room temperature applications

VELCRO® brand Adhesive 19

- Formulated especially for low energy plastics
- High tack - quick setting
- Achieves 80% bond strength in an hour; full strength in 30 hours
- Temperature operating range -40°F to 185°F

VELCRO® brand Adhesive 32

- Formulated for many substrates
- High tack - quick setting
- Achieves 80% bond strength in an hour; full strength in 30 hours
- Temperature operating range -40°F to 120°F
- Recommended for most room temperature applications

Fire Retardant

Fire retardant pressure sensitive adhesives are suitable for use in applications requiring certification to industry specifications, such as automotive.

VELCRO® brand Adhesive 8219

- A rubber-based pressure sensitive adhesive formulated especially for low energy plastics
- High tack - quick setting
- Achieves 80% bond strength in about an hour; full strength in 30 hours
- Temperature operating range -40°F to 185°F
- Certified to FAR 25.853 60 second burn test for nylon hook and loop and 12 second burn test for polyester hook and loop

VELCRO® brand Adhesive 8224


- A rubber-based pressure sensitive adhesive formulated to meet Boeing Specification BMS 8-285
- High tack - quick setting
- Achieves 80% bond strength in about an hour; full strength in 30 hours
- Temperate operating range -65°F to 160°F
- Certified to BMS 8-285 60 second burn test for nylon hook and loop and 12 second burn test for polyester hook and loop*

Choose the right pressure sensitive adhesive for your needs...

HIGH ENERGY

Aluminum
Stainless Steel
Copper
Tin
Glass
Nylon
Polyester
Epoxy Paint
Polyurethane
ABS
PVC
Acrylic
Polystyrene
Polyethylene
Polypropylene

LOW ENERGY



*Only available to Boeing companies. All others will be certified to equivalent FAR 25.853 vertical burn tests.

Solvent and Heat Activated Adhesives

Solvent

Solvent activated adhesives are recommended for applications where a more permanent bond is desired. Dry to the touch, these adhesives become tacky upon activation using solvents.

VELCRO® brand Adhesive 40

- Activated by MEK, acetone, or MCL
- Can also be used with liquid adhesive or ultrasonically welded when porous substrates exist
- Ultimate bond strength is achieved in 24 hours
- Temperature operating range -40° F to 250° F

Bonding Method Notes

If substrate is a non-porous smooth surface, apply the recommended solvent activator freely to the back of the VELCRO® brand tape with a brush or sponge applicator and allow the adhesive to become tacky. When tacky, position the tape on a cleaned substrate using finger pressure to smooth tape. (This is most important on edges and corners.) Follow a few minutes later with additional hand pressure to ensure a complete bond. Let dry overnight or speed up drying with 140° F heat source. Please be sure to use appropriate safety precautions when using a solvent activator (i.e. proper ventilation, gloves, etc.).

Heat

Heat activated adhesives are recommended for applications where a more permanent bond is desired. Dry to the touch, these adhesives become tacky upon activation using RF welding or ironing

VELCRO® brand Adhesive 43

- Activated using ultrasonic and dielectric (RF) machinery, iron-on heat, or other common heat generating equipment
- Will bond to a wide range of fabrics and plastics and has excellent water resistance
- Ultimate bond strength is achieved in 24 hours
- Temperature operating range -40° F to 160° F

Bonding Method Notes

For Ultrasonic - Precoated tape should be positioned on top of substrate. A perimeter weld at least 1/8" wide should be used to prevent peel delamination. Machine settings including pressure, weld, and dwell (hold time) should be varied according to weld patterns, materials utilized and bond strength desired.

For Dielectric (RF) - Precoated tape should be positioned on top of substrate (commonly vinyl). A perimeter weld at least 1/8" wide should be used to prevent peel delamination. Machine settings including energy level, preseal, seal, and cool times may vary according to weld patterns and materials being used.

For Iron-On - Substrate (commonly fabric) should be positioned on top of pre-coated tape. Pass warmed iron over substrate several times at incremental heat settings until adhesive softens onto substrate. Do not allow adhesive to contact hot iron surface. Allow to cool before hand peel testing.

Recommended Application Method for Solvent and Heat Activated Adhesives

Application Method	Solvent Activated Adhesive (40)	Heat Activated Adhesive (43)
MEK/Acetone/MCL	X	
RF Weld/Dielectrics	X	X
Iron-on or other heat		X

Using Our Adhesives

General Recommendations for Best Results

Surface Preparation

It is important that all surfaces be thoroughly cleaned before applying VELCRO® brand adhesives. All cleaning agents should be tested prior to use to ensure the cleaning agent will not have adverse effects on the substrate. In some circumstances, isopropyl alcohol (rubbing alcohol) may be a sufficient cleaning agent. Citrus cleaners are not recommended.

Your Plant Conditions

It is important to work in an area that is clean and free from dirt and dust in the air. The adhesive should be applied at room temperature, with the ideal room temperature between 65° F and 75° F and relative humidity 40% to 65%. Please note, the lower the humidity, the better the bond. Excessive cold, heat, dirt and relative humidity will be detrimental to your adhesive performance. If adhesive must be applied at temperatures lower than 65° F, warm the substrate and the tape to elevate temperature prior to applying. This may help the adhesive cure. If using VELCRO® brand 72 adhesive, allow full curing time before loading or cycling. It is also essential to have a well ventilated area to remove fumes and odors for the safety and comfort of your employees, and as required by your local and OSHA standards.



Limitations

VELCRO® brand adhesives are not recommended for submersion in water or on plastics with high concentrations of plasticizers. Adhesives are not washable or dry cleanable.

Recommendations for Different Types of Surfaces

Here are some additional recommendations to improve the surface area of a variety of substrates for better adhesion.

Porous Substrate

This type of surface is one that requires a primer or sealer to provide a suitable bonding area. Allow the treated surface to dry completely before applying your VELCRO® brand adhesive-backed tape. Better adhesion may be obtained when used with a liquid adhesive.

Non-Porous Substrate

VELCRO® brand Adhesive 40 is suitable for non-porous substrates. Better adhesion may also be obtained when used together with a liquid adhesive.

Smooth Surfaces

Improved bonding can be achieved by roughing up a smooth surface before applying adhesive.

Weak Substrate

Paper is a good example of a weak substrate. If the surface is weak, reinforcing the substrate with additional coverage of a liquid adhesive may improve performance.

Important Notice to Purchaser

User shall determine the suitability of the product for their intended use, and user assumes all risks and liability whatsoever in connection therewith. All statements, technical advice and recommendations contained herein are based on tests believed to be reliable, but the accuracy there of is not guaranteed, and the following is made in lieu of all warranties, expressed or implied: seller's and manufacturer's only obligation shall be to replace the quantity of product proven to be defective. Neither seller nor manufacturer shall be liable for any injury, loss or damage, direct or consequential, arising out of the use of or the inability to use the product. No statement or recommendation not contained herein shall have any force or effect unless in an agreement signed by officers of seller and manufacturer.



ISO 9001
QMI-SAI Global

THE VELCRO COMPANIES ARE WORLDWIDE LEADERS IN FASTENING SYSTEMS OFFERING A WIDE RANGE OF SOLUTIONS FROM STANDARD HOOK AND LOOP TO COMPLETE FINISHED PRODUCTS.

50 YEARS OF EXPERIENCE: WE ARE PROUD OF OUR HERITAGE IN INNOVATION, HAVING OVER 300 ACTIVE PATENTS TO OFFER BETTER SOLUTIONS TO SATISFY OUR CUSTOMERS' NEEDS.



TS 16949
QMI-SAI Global



North American Headquarters

United States

Velcro USA Inc.
406 Brown Avenue
Manchester, NH 03103
Tel: (800) 225 0180
Fax: (800) 835 2761
marketing@velcro.com
www.velcro.com

Canada

Velcro Canada Inc.
114 East Drive
Brampton, Ontario
Canada L6T 1C1
Tel: (905) 791 1630
Fax: (905) 791 5329
canada@velcro.com
www.velcro.ca

Mexico

Velcro de Mexico, S.A. de C.V.
Ave. Industria No. 102 Nave IV-A
Col. Los Reyes Pueblo
Tlalnepantla de Baz
Edo. De Mexico C.P. 54090
Tel: (+52) 55 5005 3300
Fax: (+52) 55 5384 5413
alandero@velcro.com
www.velcrodemexico.com

WORLDWIDE LOCATIONS

