

more
ways to
display



display mount options for every
application and every budget





rugged with rackmounting



video carts

- Rugged cart, mounts a single monitor up to 80" or dual monitors up to 70" & available with up to 15 rackspaces
- Display Height Adjustment: Manual with mounted display
- Storage: Rackmount - up to 15 RU; Small device – Lever Lock™
- Price: \$\$-\$\$\$



Display Size Max



VESA** Max



Display Weight Capacity



Base



Rackspaces

Color

Model	Display Size Max	VESA** Max	Display Weight Capacity	Base	Rackspaces	Color
VTC-4280S	80"	900	250 lbs.	caster	7	black/champagne
VTC-4280S-R	80"	900	250 lbs.	caster	15	black/champagne
VTC-4255D*	55" & 55"	600	250 lbs.	caster	7	black/champagne
VTC-4255D-R*	55" & 55"	600	250 lbs.	caster	15	black/champagne
VTC-5670D*	70" & 70"	600	250 lbs.	caster	7	black/champagne
VTC-5670D-R*	70" & 70"	600	250 lbs.	caster	15	black/champagne
VTC-4280S-BW	80"	900	250 lbs.	caster	7	black
VTC-4280S-RBW	80"	900	250 lbs.	caster	15	black
VTC-4255D-BW*	55" & 55"	600	250 lbs.	caster	7	black
VTC-4255D-RBW*	55" & 55"	600	250 lbs.	caster	15	black
VTC-5670D-BW*	70" & 70"	600	250 lbs.	caster	7	black
VTC-5670D-RBW*	70" & 70"	600	250 lbs.	caster	15	black

*Dual mount models allow mounting of two displays up to 55" or 70" each
 **Please consult A&E Specification for complete VESA details



sleek
with small
device storage

- Sleek design with small device storage, mounts a single monitor up to 90", models available with electric screen lift
- Storage:
Rackmount - 2 RU;
Small device – Lever Lock™ and accessory tray
- Price: \$\$-\$\$\$



Model	Display Size Max	VESA Max	Display Weight Capacity	Base	Display Height Adjustment	Color
FVS-800ESC-BK	90"	800	175 lbs.	caster	electric w/ screen mounted	Black
FVS-800ESC-WH	90"	800	175 lbs.	caster	electric w/ screen mounted	White
FVS-800SC-BK	90"	800	175 lbs.	caster	manual w/ screen removed	Black
FVS-800SC-WH	90"	800	175 lbs.	caster	manual w/ screen removed	White
FVS-800ES-BK	90"	800	175 lbs.	leveler	electric w/ screen mounted	Black
FVS-800ES-WH	90"	800	175 lbs.	leveler	electric w/ screen mounted	White
FVS-800S-BK	90"	800	175 lbs.	leveler	manual w/ screen removed	Black
FVS-800S-WH	90"	800	175 lbs.	leveler	manual w/ screen removed	White



display carts & stands



streamlined
design for
simple systems

- Built for simple systems, mounts a single monitor up to 100", models available with portrait to landscape adjustability
- Storage: optional
- Display Height Adjustment: Manual with mounted display
- Finish: Clear aluminum
- Price: \$\$-\$\$\$



Display Size Max



VESA Max



Display Weight Capacity



Base



Display Orientation Adjustment

Model	Display Size Max	VESA Max	Display Weight Capacity	Base	Display Orientation Adjustment
DS-600SC-AL	70"	600	125 lbs.	caster	portrait to landscape
DS-600SL-AL	70"	600	125 lbs.	leveler	portrait to landscape
DS-600SP-AL	70"	600	125 lbs.	plate	portrait to landscape
DS-1000SC-AL	100"	1000	175 lbs.	caster	
DS-1000SL-AL	100"	1000	175 lbs.	leveler	

DisplayStation
series

carts & stands



- Custom, scalable, heavy-duty stationary wall system - made to order and shipped within 3 weeks

monitor walls



- Stationary and mobile monitor walls ship from stock with included power, mounts 2x2 monitors up to 55"



Model	Display Size Max	VESA Max	Display Weight Capacity	Base	Color
DS-600-2X2L-AL	55"	600	352 lbs.	leveler	aluminum
DS-600-2X2C-AL	55"	600	352 lbs.	caster	aluminum

corporate headquarters

300 Fairfield Road, Fairfield, NJ 07004, U.S.A.
Voice: 800-266-7225 • Fax: 800-392-3955
International Voice: +1 973 839-1011
International Fax: +1 973 831-4982
middleatlantic.com

canada

113 Iber Road, Ottawa, Ontario K2S 1E7
Voice: 888-766-9770 • Fax: 888-599-5009
middleatlantic.ca

factory distribution

USA: New Jersey · California · Illinois
Canada: Ontario
The Netherlands: Eindhoven

