



The Anixter difference

At Anixter, we are serious about service. That is why we design personalized solutions to meet your business requirements. From a warehouse staff that manages and reduces your inventory investments to our financial offerings that help you minimize your cost of doing business, Anixter is committed to you.

Product enhancement and packaging

We provide a variety of services to enhance and tailor products according to your specifications and installation requirements, all designed to reduce your material and labor costs. These include cutting, stripping, dyeing, striping, SpeedPull®, paralleling, twisting, printing and kitting.

Inventory management

We design programs to help you manage and reduce your inventory investment. We provide just-in-time delivery, Kanban, guaranteed inventory, in-plant store, READY!™ Deployment Services and Rapid Fire inventory control.

Engineering and technical expertise

We have resources to provide you with wire and cable design engineering, technical training, product, industry and technical specialists, technical literature, application engineering and troubleshooting.

Supply chain solutions

At Anixter, we take fundamental distribution a step further by applying supply chain principles and best practices to help take the costs out of our customers' business processes. By bundling our products with our innovative supply chain

solutions, we make sure our customers get the right product, the first time.

Financial services

We provide you with the opportunity to use our financial resources instead of your own. Our service products include buy backs, guaranteed inventory programs, consigned inventories (in-plant store), inventory stock rotations, copper billing programs, consolidated invoicing, credit card ordering and cable audits.

eBusiness solutions

Anixter can provide you with real-time information on the supply chain. Solutions include Web-based supply chain visibility, eAnixter, electronic ordering and invoicing, business-to-business systems integration and customer performance reporting.



Anixter proudly distributes:

- 3M
- Adalet-PLM
- ADC
- AIW
- Allied Telesis
- Alpha Wire
- AmerCable
- American Contractor
- Amphenol
- Andrew
- APC
- Arecont
- AT&T
- Axis Communications
- BCD Video
- Belden
- Berk-Tek
- Bosch Security Systems
- Brady
- Cisco Systems
- Coleman Cable
- CommScope
- Cooper B-Line
- Corning Cable Systems
- CPI
- FCI-Burndy
- Firetide
- Flir
- Fluke Networks
- General Cable
- Greenlee
- GS Metals/Flextray
- Hammond
- Harbour Industries
- Hoffman
- Insultab
- Lake Electric
- Lapp USA
- Legrand
- Leibert
- Leviton
- Marine Tech
- Milestone
- Monroe CCI
- Nexans
- Panduit
- Pelco
- Prysmian
- Radix
- Rockbestos
- Service Wire
- Shawflex
- Siemens
- Sony
- Stran Technologies
- Superior Essex
- Surprenant
- TE Connectivity
- Thermax/CDT
- Thermo Electric
- Therm-O-Link/Vulkor
- Thomas & Betts
- Transition Networks

Anixter main marine and shipboard locations:

1750 E. Parham Road, Richmond, VA 23228 · 1.800.842.0076 | 184 Riverbend Dr., St. Rose, LA 70087 · 1.800.662.7700

MIL-Spec shipboard and aerospace cables

- MIL-DTL-24643 low smoke
- MIL-DTL-24640 lightweight low smoke
- MIL-C-17 coaxial cables
- SAE-AS22759 (M22759)
- NEMA-WC27500 (M27500)
- MIL-DTL-55021
- M16878 and other hook-up wires
- LSZH Ethernet cables (Cat 5e)

Portable and power cables

- THOF-500 enhanced
- Types SOOW/SO, SJO, SJ, SJT, ST, STO, shielded SO and others for yard operations
- Types W, G-GC, SHD-GC, MPF-GC
- DLO
- Welding cables
- Siemens crane cables
- Jumper cables 5 to 15 kV
- Shore power cables, connectors and custom assemblies

Electronic and commercial cables

- Multiconductor and multipair (shielded and unshielded)
- Coaxial cables
- Category 5e low smoke zero halogen

Rig cables

- IEEE-1580 Type P (UL, USCG, DNV, ABS, Transport Canada)
- 2 kV/600 V single-conductor power cable
- 600 V power, control and instrumentation
- Unarmored, armored, and armored and sheathed

Belden wire and cables

- LSZH ABS-rated cables

Instrumentation cables

- UL Listed PLTC
- High-temp Teflon® constructions
- Armored and direct burial
- Thermocouple and thermocouple extension cable
- Fiber optic

Security solutions

- Video surveillance
- Access control
- Security consoles
- Sound and paging systems
- Fire and intrusion products
- Low-voltage and fiber cabling
- Accessories

Connectors, tools and other accessories

- MIL-C-83522 ST
- MIL-PRF-29504 termini
- MIL-PRF-28876 multichannel
- TFOCA tactical
- Fiber optic connectors
- AA59729 fiber furcation units
- Blolite® blown fiber optic accessories
- Termination tools
- Test equipment
- Cable glands
- Terminal tubes
- Compression lugs
- Cable ties

Fiber

- MIL-PRF-85045 fiber optic cables (General Cable)
- MIL-PRF-49291 blown fiber Blolite (General Cable)
- Mil-Spec fiber optic cables (General Cable)
- M85045 military fiber optic cables
- MIL-PRF- 85045 Blolite fiber tubing
- MIL-PRF49291 Blolite
- Blolite connectors and parts
- Military fiber jumpers

Anixter's supply chain solutions model

- Evaluate all processes involved with material procurement and deployment
- Scale model to match project scope
- Determine specific areas to streamline - order entry, material management, delivery, freight, etc.
- Develop a well-defined program to minimize costs while maximizing efficiency and reducing risk



About Anixter: anixter.com/aboutus
Legal Statement: anixter.com/legalstatement

14D2829X00 © 2013 Anixter Inc. · 10/14

Anixter Inc. World Headquarters
 2301 Patriot Boulevard
 Glenview, Illinois 60026
 224.521.8000

1.800.ANIXTER | anixter.com

