


UTG SOLUTIONS BRIEF FLUKE NETWORKS



TEST AND MEASUREMENT

The Utility Grade INFRASTRUCTURE (UTGSM) programme has been developed alongside world-class global Technology Alliance Partners. These UTG-recommended components from Fluke Networks enable you to support the rapid evolution of technology in today's building environments.

PRODUCT OVERVIEW

Fluke Networks' UTG solutions provide field testing to validate UTG performance beyond industry standards. The below cable certifier recommendations complement a full UTG solution providing access to exclusive Fluke field test limits that meet the UTG Framework.

INTER-BUILDING | INTRA-BUILDING | CONNECTED CEILING | BUILDING-EDGE | EXTENDED-EDGE

VERSIV CABLE CERTIFIER

The VersivTM family accelerates every step of the certification process. Future-ready design supports copper certification, fibre loss, OTDR testing and hardware upgrades. The revolutionary ProjXTM management system and TaptiveTM user interface ensures jobs are done right the first time. Analyse test results and create professional test reports using LinkWareTM management software.

FEATURES AND BENEFITS

- Exclusive UTG field test limits that perform at 100, 150, and 185 meters meeting the UTG Framework
- VersivTM modular design supports copper certification, fibre optic loss, OTDR testing and fibre end-face inspection
- Unmatched speed for Cat 6A, 8, Class FA, I/II and all current standards
- ProjXTM system manages job requirements and progress from set-up to systems acceptance, making sure all tests are completed correctly
- TaptiveTM user interface simplifies set-up, and eliminates errors
- Analyse test results and create professional test reports using LinkWareTM management software
- Graphically displays the source of failures including crosstalk, return loss and shield faults for faster troubleshooting
- Intertek Verified to TIA Level 2G and IEC Level VI accuracy requirements to 2000MHz – the most stringent accuracy requirement
- Built in Alien Crosstalk testing
- Compatible with LinkWare Live

Fluke Part #	Anixter Part #	Product Details
DSX2-8000/GLD INT	964284	DSX-8000 2 GHz up to Cat 8 CableAnalyzer™ with 1 Yr Gold Support
DSX2-8000QI/G INT	964286	DSX-8000QI 2 GHz up to Cat 8 CableAnalyzer™ w/SM and MM fibre loss testing, fibre inspection and 1 Yr Gold Support
DSX2-8000QOI/G INT	964291	DSX-8000QI 2 GHz up to Cat 8 CableAnalyzer™ w/SM and MM fibre loss, OTDR testing, fibre inspection and 1 Yr Gold Support
DSX2-8000PRO/G INT	964293	DSX-8000-Pro 2 GHz up to Cat 8 CableAnalyzer™ w/SM and MM fibre loss, OTDR testing, fibre inspection, full accessories and 1 Yr Gold Support
DSX2-5000/GLD INT	964287	DSX-5000 1 GHz up to Cat 6a CableAnalyzer™ and 1 Yr Gold Support
DSX2-5000QI/G INT	964288	DSX-5000QI 1 GHz up to Cat 8 CableAnalyzer™ w/SM and MM fibre loss testing, fibre inspection and 1 Yr Gold Support
CFP2-100-Q/GLD INT	964290	CFP2-100-Q CertiFiber® Pro Optical Loss Test Set for SM and MM with 1 Yr Gold Support
OFP2-100QI/GLD INT	964289	OFP2-100-QI OptiFiber® Pro OTDR for SM and MM with inspection and 1 Yr Gold Support

Note: The above part numbers are featuring Fluke's top products within the UTG space and are not inclusive of all Fluke's available configurations.

 [FOR MORE DETAILS, VISIT ANIXTER.COM/EMEA/UTG](https://www.anixter.com/emea/utg)