



## BUSHING CONNECTION ANIMAL COVER (BCAC) WILDLIFE AND ASSET PROTECTION PRODUCTS

### KEY FEATURES

- Reliable protection from animal-caused outages
- Fast and versatile installation
- High-performance materials for extreme durability
- Cover gripper attachment facilitates hot-stick installation from pole or bucket
- Step latching mechanism for craft-friendly installation
- REACH and RoHS compliant

TE Connectivity's (TE) Raychem BCAC hot-stickable insulating cover is designed to prevent animal caused outages on pole-top transformer equipment ranging from 15 kV to 36 kV.

TE's BCAC Insulating Cover range has been successfully eliminating outages from all types of animals for years. This cover has been designed to provide the same great protection with enhanced features.

The BCAC -5D cover uses a scissor action design to allow for live installations on bushing skirts, ranging in size from 1.7" (43 mm) through 2.7" (68mm) in core diameter and 3.0" (75 mm) through 4.75" (120 mm) in shed diameter. The scissor action translates the force on contact with the bushing core to a rotating action that closes the cover around the bushing.

Superior high-voltage outdoor materials are used in the BCAC cover design. The rugged, non-tracking, UV-resistant polymer ensures long-term performance even in the most extreme environmental conditions.

**Customers can count on consistent, high quality products, driven by TE's proven innovation and backed by our extraordinary customer support.**



TE's wildlife and asset protection products and systems of tubes, tapes, sheets, pre-formed covers and barriers provide a proven, cost-effective and easy-to-install solution to bird, animal and weather related outages.

PRODUCT PERFORMANCE		
TESTING		
<b>AC Withstand</b>		<b>Wind Tunnel</b>
20 kV IEEE-4: 1978, no flash over		70 MPH for 10 mins, no dislodging of cover from insulator location
Physical		
<b>Key Material Property</b>	<b>Test Method</b>	<b>Material Requirements</b>
<b>Tensile Strength</b>	ATSM D638	17 MPa (2450 psi) min.
<b>Ultimate Elongation</b>	ASTM D638	25% min.
Electrical		
<b>Key Material Property</b>	<b>Test Method</b>	<b>Material Requirements</b>
<b>Dielectric Strength</b>	ATSM D257	150 kV/cm min. (2.5 mm)
<b>Tracking and Erosion Resistance</b>	ATSM D2303 Step Voltage Method (initiate at 2.5 kV)	No tracking erosion to top surface or flame failure after: 1hr at 2.5 kV 1hr at 2.75 kV 1hr at 3.00 kV 1hr at 3.25 kV 1hr at 3.5 kV

PRODUCT SELECTION INFORMATION - DIMENSIONS IN INCHES (MM)					
Description	Insulator Core Range	Insulator Shed Range	Cover Height	Color	Standard Pack Size
BCAC-5D/8 (B12)	1.7 - 2.7 (43-63)	3.0 - 4.8 (75 - 122)	8.0 (203)	Red	12
BCAC-G-5D/8 (B12)	1.7 - 2.7 (43-63)	3.0 - 4.8 (75 - 122)	8.0 (203)	Gray	12
BCAC-7D/10 (B6)	1.5 - 4.25 (38 - 108)	4.0 - 6.8 (102 - 173)	10.5 (266)	Red	6
BCAC-G-7D/10 (B6)	1.5 - 4.25 (38 - 108)	4.0 - 6.8 (102 - 173)	10.5 (266)	Gray	6
BCAC-8D/14 (B6)	1.7 - 5.04 (43 - 125)	5.0 - 8.0 (125 - 203)	14.0 (355)	Red	6
BCAC-G-8D/14 (B6)	1.7 - 5.04 (43 - 125)	5.0 - 8.0 (125 - 203)	14.0 (355)	Gray	6

TECHNICAL REPORT	
EDR-5339	Bushing Connection Animal Cover (BCAC-5D/8) Mechanical/Electrical Evaluation
UVR-8209	Material Test Report

INSTALLATION INSTRUCTIONS	
EPP-3225-10/18	Installation Instructions for BCAC-5D/8
PII-55169	
EPP-3226-10/18	Installation instructions for BCAC-7D/10 and BCAC-8D/14
PII-55647	



[te.com/energy](http://te.com/energy)

©2011, 2012, 2014, 2016 TE Connectivity Ltd. family of companies. All Rights Reserved. EPP-2612-DDS-11/18-EN

Raychem, TE Connectivity and TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

**FOR MORE INFORMATION:  
TE Technical Support Centers**

USA: + 1 800 327 6996  
 Canada: + 1 (905) 475-6222  
 Mexico: + 52 (0) 55-1106-0800  
 Latin/S. America: + 54 (0) 11-4733-2200  
 France: + 33 380 583 200  
 UK: + 44 0870 870 7500  
 Germany: + 49 896 089 903  
 Spain: + 34 916 630 400  
 Italy: + 39 333 250 0915  
 Benelux: + 32 16 508 695  
 Russia: + 7 495-790 790 2-200  
 China: + 86 (0) 400-820-6015