

SELECTING AN ETHERNET TO SERIAL CONVERTER FOR YOUR NEXT PROJECT

Use the selection tables on p2 to quickly narrow your search for an Ethernet to Serial Converter that best suits your next project. Below are a few helpful questions to help narrow the selection:

- **How many serial ports do you need?**
 - B+B SmartWorx offers 1, 2, 4, 6 and 8 port solutions
- **What is the serial data type of the device you are connecting too?**
 - RS-232
 - RS-422/RS-485 (2-wire or 4-wire connections)
 - Current Loop
- **Does the application need to support Modbus protocol?**
- **What about the Ethernet connection?**
 - One Ethernet port will get the job done.
 - Two Ethernet ports may eliminate the need for an Ethernet switch.
 - A fiber port may eliminate the need of a media converter at a remote location.
 - What about a WiFi interface? This is a great choice for any application that requires mobility.
- **Should serial isolation be considered to help protect against surges, spikes and grounding issues?**
- **What about the physical serial connector – is a DB9 or a Terminal Block preferred?**
 - Most prefer a DB9 for an RS-232 connection and a Terminal Block for RS-422/485 connections.
- **What mounting option best suites the application?**
 - DIN rail mountable? (good for in-cabinet designs)
 - Panel mountable? (use on a desktop or flat panel mounted)
 - 19-inch rack?
- **What environmental or safety aspects should be considered?**
 - Are there any temperature concerns based on where the Ethernet to Serial converter will be located?
 - Is a UL Class I/Division 2 rating required for the application?
 - Are shock, vibration or drop testing specifications required for the application?
- **Once you have a product selected, you should ask just a few more questions:**
 - Do you have all the accessories needed to make the needed connections?
 - Cables, Power Supplies, Cabinets, Surge Protection? Ethernet Switches or other Ethernet Infrastructure devices?
 - When do you need product or samples for proof of concept? When do you plan to go to full production?



Assistance

If you need additional product selection help, contact B+B SmartWorx technical support online chat at www-bb-elec.com.

ETHERNET TO SERIAL CONVERTER

PRODUCT SELECTION GUIDE (continued)



Virtual COM Software

Modbus Protocol Support

Series:	VESP211	VESR321	VESR900	VESR400	ESP906CL	xSE-x00D	ABDN-SE-DP551	ABDN-SE-IN	MESP211	MESR900	MESR321	MESR400
ETHERNET												
Copper Ports	1	2	1,2	2	1	1	0	1	1	1,2	2	2
Fiber Ports		Optional	Optional	Optional						Optional	Optional	Optional
WiFi Ports							1	1				
SERIAL												
Port Count	1	1	1,2	4	6	1,2,8	1	1,2	1	1,2	1	4
DB9	232	232	232/422/485	232/422/485	232/422/485	232, 422/485	232/422/485	232/422/485	232/422/485	232/422/485	232	232/422/485
Terminal Block	422/485	422/485	232/422/485	232/422/485	Current Loop				232/422/485	232/422/485	422/485	232/422/485
Isolation		2kV			Current Loop						2kV	
SPECIFICATIONS												
Temperature	-40 to 80°C	-40 to 80°C	-40 to 80°C	-40 to 80°C	0 to 40°C	0 to 70°C	-20 to 85°C	-40 to 85°C	-40 to 80°C	-40 to 80°C	-40 to 80°C	-40 to 80°C
Power DC	10 to 30VDC	10 to 48VDC	10 to 48VDC	10 to 48VDC	5 & 36VDC	5VDC	5VDC	5 to 36VDC	10 to 30VDC	10 to 48VDC	10 to 48VDC	10 to 48VDC
Power Supply Included	Yes				Yes	Yes	Yes		Yes			
Dual Power Inputs		TB & Barrel		TB & Barrel							TB & Barrel	TB & Barrel
Mounting	Panel	DIN/Panel	DIN	DIN/Panel	Panel	Desktop	Desktop	Panel	Panel	DIN	DIN/Panel	DIN/Panel
19-inch Rack						8 port models						
Class 1/Division 2			Yes	Yes						Yes		Yes
MODEL/SKU#												
	VESP211	VESR321	VESR901	VESR424D	ESP906CL	DSE-100D	ABDN-SE-DP551	ABDN-SE-IN5410	MESP211D	MESR901	MESR321	MESR424D
	VESP211-232	VESR321-ML	VESR902D	VESR424D-MC		ESE-100D		ABDN-SE-IN5420	MESP211D-EU *	MESR902T	MESR321-ML	MESR424D-MT
	VESP211-EU *	VESR321-SL	VESR902T	VESR424D-MT		ESE-400D			MESP211D-UK +	MESR921	MESR321-SL	MESR424D-SC
	VESP211-UK +		VESR921	VESR424D-SC		SSE-100D			MESP211T	MESR921-MC		MESR424T
	VESP211-232-EU *		VESR921-MC	VESR424D-ST					MESP211T-EU *	MESR921-MT		MESR424T-MT
	VESP211-232-UK +		VESR921-MT	VESR424T					MESP211T-UK +	MESR921-SC		MESR424T-SC
	VESP211-485		VESR921-SC	VESR424T-MC						MESR921-ST		
	VESP211-485-EU *		VESR922T	VESR424T-MT						MESR922T		
	VESP211-485-UK +		VESR922T-MC	VESR424T-SC						MESR922T-MC		
			VESR922T-MT	VESR424T-ST						MESR922T-MT		
			VESR922T-SC							MESR922T-SC		

* European power supply included.
+ United Kingdom power supply included.