


PRODUCT SOLUTIONS BRIEF

APC BY SCHNEIDER ELECTRIC

HEALTHCARE FACILITY POWER OPTIMIZATION



Through our strong global partnerships and alliances with manufacturers such as APC by Schneider Electric, we are able to present you with the following offering to meet your specific healthcare requirements.

Smart-UPS™ On-Line

APC by Schneider Electric's Smart-UPS On-Line provides high-density, double-conversion online power protection for servers, voice/data networks, medical labs and light industrial applications. The Smart-UPS On-Line is capable of supporting loads from 3 kVA to 10 kVA in a rack/tower convertible chassis. When business-critical systems require runtime in hours, not minutes, Smart-UPS On-Line can be configured with multiple battery packs to meet aggressive runtime demands.



Smart-UPS with additional battery pack.

CHALLENGE SOLVERS

- Best-in-class power density: more real power in watts, 0.9 pf on the 3 kVA, 0.85 pf on 5 kVA, Unity on 6 kVA–10 kVA units
- High-efficiency green mode: achieves 98 percent efficiency, which saves utility and cooling costs without compromising performance or reliability
- Built-in energy meter: measures energy use and displays UPS efficiency in various modes of operation for easy energy tracking
- Intelligent battery management: the UPS can inform the user which batteries need to be replaced and auto detect when additional battery packs are added

THE ANIXTER APPROACH

• Backup Power

Provide optimal settings for quality patient care with an always-on environment.

• Efficient Power

Consider highly-efficient solutions that maximize power quality and minimize operational expenses.

• Monitored Power

Adopt an integrated power solution that can be metered, monitored and designed for continuity.

Life Is On




WHAT WE HEAR

Healthcare stakeholders are dealing with a variety of challenges:



Meeting **ENERGY EFFICIENT** goals



PREVENTING accidental outages



Ensuring an **ALWAYS ON** environment



Reducing **UTILITY COSTS**



Restrictions of **LEGACY ELECTRICAL INFRASTRUCTURE**

THE APC SOLUTION

POWER CAPACITY

3–10 kVA models

EXTENDED RUNTIME

External batteries

CONFIGURE OPTIONS

Management cards
Environmental sensors

anixter.com/shopapc

Infrastructure as a Platform
by Anixter

Infrastructure as a Platform by Anixter provides a practical, configurable and integrated approach to retrofitting or building a critical power chain in your healthcare environment.

CONFIGURE

We help you discover and map your specific needs to the best solution.

- Management card
- Battery packs
- Service bypass panels
- Rail kits

BUNDLE

Your validated, preconfigured solutions are packaged and site ready.

- Power management software
- Intelligent PDUs
- Racks and cabinets
- Locking power cords

DEPLOY

Controlled, repeatable solutions are delivered on time and under budget.

- Custom packaging and labeling
- Time-sensitive delivery options
- Staged project shipping
- Tailored last-mile delivery

APC SMART-UPS ONLINE FEATURES

✓ ENSURES AN ALWAYS ON ENVIRONMENT

- Ability to control a group of output load receptacles independent from the main UPS
- Ability to remotely shutoff the UPS in the event of a fire or other emergency
- Three-year warranty on electronics

✓ MEETS ENERGY EFFICIENT GOALS

- Features embedded network management card with environmental monitoring
- Schedules time off to conserve energy
- Measures energy usage and displays UPS efficiency in various modes of operation



Supports loads from 3kVA to 10kVA in a rack/tower convertible form.

> FOR MORE DETAILS VISIT ANIXTER.COM/SHOPAPC

About Anixter: anixter.com/aboutus

Legal Statement: anixter.com/legalstatement

At Anixter, we enable the connected world. By building, connecting, protecting and powering valuable assets and critical infrastructures, we help to sustain and grow businesses and communities worldwide. We accomplish this by offering full-line solutions, technical intelligence, supply chain expertise and an unmatched global distribution network.

1.800.ANIXTER | anixter.com

