



A *NewellRubbermaid* Brand

©2013 DYMO. All rights reserved.
Atlanta, GA 30328
800-426-7827
www.dymo.com



DYMO Industrial Labeling Full-Line Catalog

Time is money. Save more of both.





Leave **any job** looking better than you found it.

Designed based on input from professional installers, DYMO® industrial labelers and labels are tough, affordable and long-lasting. They're loaded with convenient features that speed up your productivity – and help you save time and money every day.

The Rhino™ Product Line-up:



Rhino™ M1011



Rhino™ 4200



Rhino™ 5200



Rhino™ 6000

Thermal transfer printing means labels won't smudge, smear or fade. Choose up to a one-inch label width in a broad assortment of materials and colors that meet OSHA, ANSI, and ISO standards.

All DYMO Industrial labels are distributed from an easy-to-load cartridge, and with a split-back design, peeling and applying is quick and easy.



DYMO Industrial Labels

DYMO Industrial Labels are available in:

- Flexible Nylon
- Permanent Polyester
- Indoor/Outdoor Vinyl
- Heat-Shrink Tube
- Non-Adhesive Tag
- Self-Laminating

Complete your work with pride and professionalism.

No matter what industry you work in, DYMO® Industrial products give your installation work a clean, professional look that enhances your reputation. Our label printers and labels make it easier than ever to get results that meet industry standards – as well as yours. All our products stand up to the toughest conditions your industry can dish out.

One-touch "Hot Keys" – a DYMO exclusive – save you time.



Wire & Cable Wraps

Advanced wrap function automatically selects the right label and text size, based on the wire guage, cable diameter or cable type.



Panels & Blocks

Instantly format and serialize labels for patch panels, terminal blocks and modular components.



Flags

Create perfectly spaced flag labels allowing visibility from any angle.



Fixed-Length & Vertical

Fixed-length key automatically centers and prints fixed-length labels to your requirements. With the press of a button, align text vertically for easy-to-read labels.



Electrical Features

Pre-formatted for creating electrical panel, breaker, and module labels.



Symbols & Terms Library

Provides fast access to common datacom, electrical, pro AV, security and safety symbols; including: ohms, earth, phone, data and fax. Select and print 150+ industry terms from a built-in library.

Exclusive, one-touch "HOT KEYS"

Shortcut keys for creating and formatting wire and cable wraps, flags and barcodes, patch panel, electrical panel, terminal and 110 block, vertical and fixed-length labels.

HOT KEYS



Wire & Cable Wraps
Panels & Blocks
Flags
Fixed Length & Vertical
Electrical Features
Symbols & Terms Library

Online resources:

Designed for end users, installers and distributors.

Visit | www.dymo.com

And check out our comprehensive resource collection for the full line of products. Learn about features, get step-by-step product trainings, view educational videos, industry blogs, upcoming events and more.

We've created templates for equipment from Belden, Honeywell, Leviton and other leading manufacturers.

Online resources include:

- 1 Manufacturer Templates**
 Download templates with exact label spacing for Patch Panels, 110 and Terminal blocks
- 2 Upcoming Tradeshows**
 Find a tradeshow near you and stop by to check us out
- 3 Training Classes**
 Sign up for online training classes led by industry experts
- 4 Software***
 Download the latest version of Rhino Connect™ Software
* Compatible with Rhino 6000
- 4 Industrial Labels**
 Learn about our broad label assortment, including compliance with industry standards and certifications
- 6 Product Training**
 Watch step-by-step product trainings and educational videos



Download Manufacturer Templates

Just download the template, open in Rhino Connect™ software, and add text to create labels that fit the equipment perfectly – no measuring required. New templates added regularly.

TEMPLATES

Honeywell
Security &
Communications



COMMSCOPE



Advanced Datacom

Rhino™ 6000

Advanced Labeling Tool with PC Connectivity

Feature-packed industrial labeler with PC connection.

Bring the tough, portable Rhino 6000 to any jobsite – it's packed with time-saving shortcuts for labeling any installation quickly and professionally. Connect it to your PC, and use RHINO CONNECT™ software to create labels on your computer, and download them to your labeling tool for even faster labeling on site. Works with 32- and 64-bit Windows® XP, Windows Vista® and Windows® 7.

DYMO Rhino 6000 features:

- 1 **Connects to PC via USB cable.** Use RHINO CONNECT™ software to create labels on your PC and download them to the labeler for printing on site
- 2 **Meets all ANSI and TIA/EIA-606-B** industry labeling standards
- 3 **Exclusive, one-touch “Hot Keys”** provide shortcuts to size, shape and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications including 5 line print capability
- 4 **Prints 6 different barcode types** including Code 39 and Code 128
- 5 **Powerful serialization**—Built-in wizards for simple and advanced serialization
- 6 **Symbol library** with more than 250 pre-programmed industry symbols, terms, fractions and punctuation marks
- 7 **Last-label memory** and storage for up to 1000 of the labels you use most



Included

Up to



Item No: 1734519

RHINO 6000 SINGLE UNIT

Box includes:

- Rhino 6000 printer
- 1" black on white vinyl tape
- Rechargeable lithium-ion battery
- AC adapter
- Quick Reference Guide
- Registration card

Rhino 6000 Hard Case Kit

The ultimate in portable, professional labeling.

The Rhino 6000 Hard Case Kit offers leading technology in an all-in-one package. Included RHINO CONNECT™ Software offers the ultimate versatility to plan installations ahead of time and implement directly at the worksite.



Item No: 1734520

RHINO 6000 HARD CASE KIT

Kit includes the Rhino 6000 printer, PLUS:

- Rhino CONNECT™ Software*
- Durable hard carry case
- 3/4" black on white vinyl tape
- 3/8" black on white vinyl tape
- Rechargeable lithium-ion battery
- AC adapter and USB cable
- Quick Reference Guide
- Registration card

* Software only in the Hard Case Kit



Outperforms industrial labelers costing twice as much.

Label up to 77% faster with the portable, affordable DYMO Rhino 5200.* Press one "Hot Key" to format text into perfect patch panel labels; press another to print matching cable flags or face plate tags, without retyping! It's just as easy to print cable wraps, terminal/110 block labels, barcodes & more.

DYMO Rhino 5200 features:

- 1 Meets all ANSI and TIA/EIA-606-B industry labeling standards
- 2 Exclusive one-touch "Hot Keys" automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, wire and cable wraps, vertical and fixed-length applications
- 3 Prints Code 39 and Code 128 barcodes on 3/4"-wide labels – ideal for asset management
- 4 Uses DYMO Industrial labels with chemical-, heat- and UV-resistant materials; also prints directly on heat-shrink tubes and non-adhesive labels
- 5 Large 14-character, two-line backlit display
- 6 100-label memory for storing commonly used labels

*Based on the independent testing of the DYMO Rhino 5200 vs. the Panduit LS8, Brady BMP21, Brother PT1650 measured in the number of key strokes when making a patch panel, all associated wire labels and face plate labels.



Capable

Up to

3/4"
19 mm

Item No: 1755749

RHINO 5200 SINGLE UNIT

Box includes:

- Rhino 5200 printer
- 3/4" black on white vinyl tape
- Quick Reference Guide
- User Manual on CD-rom

Rhino 5200 Hard Case Kit The "ready-to-go" labeling solution.

For the fastest, easiest way to use the Rhino 5200 professional portable labeler, get hold of this complete kit, including rugged carry case. It has all you need to hit the ground running.



Item No: 1756589

RHINO 5200 HARD CASE KIT

Kit includes the Rhino 5200 printer, PLUS:

- Durable hard carry case
- Rechargeable lithium-ion battery
- 3/4" black on white vinyl tape
- 3/8" black on white vinyl tape
- AC adapter
- Quick Reference Guide
- User Manual on CD-rom

Facility, Security, and Pro AV

Rhino™ 4200

All-Purpose Labeling Tool with QWERTY Keyboard

Compact, time-saving labeling for on-the-go pros.

Print labels 57% faster than the competition with the DYMO Rhino 4200.* Easily navigate the familiar QWERTY keyboard. Use one-touch "Hot Key" shortcuts to quickly create and format wire/cable wraps, flags, Code 39 and Code 128 barcodes, fixed-length labels and more. Print labels up to 3/4" wide in a variety of materials and colors - PLUS print directly on heat-shrink tubes.

DYMO Rhino 4200 features:

- Easy to navigate computer-style QWERTY keyboard**
Quick and comfortable text entry
- One-Touch "Hot Keys" – a DYMO exclusive**
Use up to 45.5% fewer keystrokes to create a label than the competition**
- Industrial-strength labeling versatility**
Print 1/4", 3/8", 1/2" and 3/4" wide labels in a variety of materials and colors – PLUS print directly on heat-shrink tubes
- NEW "Favorites" key**
Single-key access to your most commonly used labels, symbols and terms
- NEW "Custom" key prevents needless repetition**
Customize and save settings for individual label formats

* Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 in default settings

**Based on independent testing of Rhino 4200 vs. Brother PT-1400 and Brother PT-7100 for wire/cable wrap and flag labels



Capable

Up to

3/4"

19 mm

Item No: 1801611

RHINO 4200 SINGLE UNIT

Box includes:

- Rhino 4200 printer
- 1/2" black on white vinyl tape
- Quick Reference Guide



QWERTY

Rhino™ 4200 Hot Keys



Breaker/Module



Code 39/Code 128



Wire/Cable/Flag



Rotate/Align



General/Fixed



Item No: 1835374

RHINO 4200 SOFT CASE KIT

Kit includes the Rhino 4200 printer, PLUS:

- Protective carry case
- Rechargeable lithium-ion battery
- 1/2" black on white vinyl tape
- AC adapter
- Quick Reference Guide

Rhino CONNECT™ Software

For use with the Rhino 6000 labeler.

Item No: 1738636

On-site industrial labeling, made quicker.

The fastest, most cost-effective solution for panel builders, harness shops, and any other business that labels in high volume on a daily basis.

System requirements:

PC Windows® 7, Windows® XP or Windows Vista®
USB port, 10MB of hard disk space, and CD-ROM Drive

Laptop and Rhino printer NOT INCLUDED



Rhino Carry Cases

Store and protect your Rhino in a durable case.



Item No: 1738638
RHINO 6000
Hard Carry Case

Item No: 1760413
RHINO 5200
Hard Carry Case

Item No: 1835375
RHINO 4200
Soft Carry Case

Rhino AC Adapter and Rechargeable Lithium-ion Batteries

Run or recharge your Rhino labeler and eliminate AA battery cost and waste.



Item No: 15519
Universal AC Adapter
For Rhino 4200, 5200,
and 6000

Item No: 1759398
Rechargeable Battery
For Rhino 4200 and 5200
(Requires AC Adapter
for charging)

Item No: 1738637
Rechargeable Battery
For Rhino 6000
(Requires AC Adapter
for charging)



Printer Selection Guide

Rhino™



IND	Overview	Rhino 6000 Item No: 1734519 (Single Unit) Item No: 1734520 (Hard Case Kit)	Rhino 5200 Item No: 1755749 (Single Unit) Item No: 1756589 (Hard Case Kit)	Rhino 4200 Item No: 1801611 (Single Unit) Item No: 1835374 (Soft Case Kit)
Barcodes		6	Code 39 + Code 128	Code 39 + Code 128
Patch Panels		YES	YES	-
110 Blocks		YES	YES	-
Terminal Blocks		YES	YES	-
Flags & Cable Wraps		YES	YES	YES
Fixed & General		YES	YES	YES
Breakers & Modules		YES	YES	YES
Self Laminating		YES	-	-
Serialization		Advanced	Advanced	Simple
Pre-programed Symbol Library		YES	YES	YES
Pre-programed Term Library		YES	-	YES
Customizable Library		YES	YES	YES
Memory		1000 Labels	100 Labels	25 Labels
PC Connectivity (USB)		YES	-	-
Rhino Connect™ Software Compatible		YES	-	-
Import Graphics		YES	-	-
Import Data from Excel		YES	-	-
Import DataCom Templates		YES	-	-
Li-ion Rechargeable Battery		Included	Capable	Capable
Cutter Type		Electronic	Manual	Manual
Keyboard Type		ABC	ABC	QWERTY
Backlit Display		YES	YES	YES
Integrated Rubber Bumper		YES	YES	Partial
Multi-Label View		YES	YES	YES
Lanyard Loop		YES	YES	-
Number of Styles		5	5	5
Maximum Lines of Print		5	5	5
Number of Character Sizes		7	7	7
Printing Process		Thermal Transfer	Thermal Transfer	Thermal Transfer
Print Resolution		180 dpi	180 dpi	180 dpi
Languages		11	17	20
Dimensions		9.7"H x 5.4"W x 2.5"D	9.2"H x 4.9"W x 2.5"D	7"H x 4.6"W x 2.25"D
Weight		4 Lbs	2 Lbs	2 Lbs
Tape System		Rhino Industrial Labels	Rhino Industrial Labels	Rhino Industrial Labels
Tape width in inches		1/4", 3/8", 1/2", 3/4", 1"	1/4", 3/8", 1/2", 3/4"	1/4", 3/8", 1/2", 3/4"

Industrial Embosser

Rhino™ M1011

Metal Embossing Tool



Innovation that began over 40 years ago and continues today.

The Rhino™ M1011 embosses 1/2" stainless steel and aluminum labels – with or without adhesive – that resist corrosion due to extreme weather, temperature, chemical, and UV exposure. This tough, durable embosser features an easy-to-use label cutting handle (cuts rounded edges), hole and cable tie punches, a trailing edge measuring gauge, and much more.

DYMO Rhino M1011 features:

- 1 **Uses 1/2" Stainless Steel & Aluminum labels**
- 2 **Built-in hole punch** for creating hanging, screw-on or nail-on labels
- 3 **Built-in cable tie slot punch** for cable marking
- 4 **Built-in measuring gauge** – accurately set length of leading and trailing label edge
- 5 **Easy-to-use cutting handle** makes cutting stainless steel labels effortless – Cuts slightly rounded edges
- 6 **Print standard or reverse script labels** – both character wheels included



1/2"
12 mm



Item No: **1011-05**

RHINO M1011 KIT

Box includes:

- Rhino M1011 Metal Tape Embosser
- Horizontal .188" Character Wheel
- Reverse Image Wheel
- 1/2" x 16' Non-Adhesive Aluminum Tape
- 1/2" x 21' Non-Adhesive Stainless Steel Tape
- Hard Carry Case


Rhino M1011 Embossing Labels

For heavy-duty, extreme-condition labeling.

Aluminum and stainless steel labels have excellent resistance to chemicals, extreme weather conditions, high and low temperatures and abrasion. Ideal for marking pipelines, underground cables, engine parts, building materials and much more.

Metal Labels (Box of 10 Rolls)			1/2" (12mm)
Part #	Description	Length	Color
310-00	Non-Adhesive Aluminum 1/2" (12mm)	16' (4,80m)	Aluminium
325-00	Non-Adhesive Stainless Steel 1/2" (12mm)	21' (6,40m)	Stainless
358-00	Adhesive Aluminum 1/2" (12mm)	12' (3,65m)	Aluminium

The right label for virtually every situation and surface.



Indoor/Outdoor Vinyl

For general labeling or extreme conditions. Vinyl labels offer moisture, chemical and UV resistance, making them ideal for labeling both indoors and outdoors. Available in the widest range of colors that adhere to OSHA, ANSI and ISO color standards.

UL recognized as a component to UL 969

Flexible Nylon

For labeling wires, cables and rounded surfaces. Flexible Nylon labels conform and stick tightly to wires, cables, curved and textured surfaces. Tear-proof material resists damage when pulled through tight spaces or conduits.

UL recognized as a component to UL 969

Permanent Polyester

For labeling panels, blocks, faceplates, shelves, bins, beams and more. Permanent Polyester labels have a polished finish that leaves your work looking professional. Available in smaller widths that fit most patch panels, blocks and other distribution panels.

UL recognized as a component to UL 969

Heat-Shrink Tube

For high-end cable identification. A 3:1 shrink ratio helps ensure a secure fit on wires and cables. Print directly on Heat-Shrink Tubes with any DYMO Industrial labeling tool.

Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
UL recognized as a component to UL 224

Non-Adhesive Tag

For sliding into racks or faceplates that do not require adhesive. Made from polyester for increased durability.

Self-Laminating











Self-Laminating labels protect your printed area from exposure to oil, solvents, water and abrasion when applied to wires and cables.

All DYMO Industrial labels are RoHS compliant.

For technical specifications on all DYMO Industrial label types, please visit our website at:


www.dymo.com

How to choose the right DYMO Industrial label:

ENVIRONMENT	 Heat/Cold Resistant	 UV Light Resistant	 Oil Resistant	 Water Resistant	 Chemical Resistant	 Color Coding
SURFACE						
 Cable/Wire	Flexible Nylon Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl Heat-Shrink Tube	Indoor/Outdoor Vinyl
 Curved Surface	Flexible Nylon Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl Flexible Nylon	Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
 Flat Surface	Permanent Polyester Flexible Nylon	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Permanent Polyester Indoor/Outdoor Vinyl	Indoor/Outdoor Vinyl
 Textured Surface	Permanent Polyester Flexible Nylon	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl Permanent Polyester	Indoor/Outdoor Vinyl

Top = Best Option Bottom = Alternate Option

Available DYMO® Industrial label widths and colors:



IND	LABEL APPLICATIONS	LABEL COLOR	1/4"	3/8"	1/2"	3/4"	1"
			6mm	9mm	12mm	19mm	24mm
Labels that stick and stay stuck. DYMO Industrial labels are tough— jobsite tested and UL recognized. Labels won't smear or fade and are built with industrial-strength adhesives to resist moisture, UV light and extreme temperatures. Whether you are labeling to OSHA, ISO and ANSI color standards or labeling in harsh conditions, DYMO Industrial labels have you covered. DYMO Industrial labels are designed to work exclusively with Rhino™ printers and to perform on a variety of surfaces. LEARN MORE: www.dymo.com	BLACK ON WHITE	-	18443	18444	18445	1805430	
		BLACK ON YELLOW	-	-	18432	18433	1805431
		BLACK ON ORANGE	-	-	18435	18436	1805427
		BLACK ON GREY	-	-	1805413	1805419	1805425
		WHITE ON RED	-	-	1805416	1805422	1805429
		WHITE ON BLACK	-	1805437	1805435	1805436	1805432
		WHITE ON GREEN	-	-	1805414	1805420	1805426
VINYL Length 18' 5.5m - UL Recognized Component to UL969 - RoHS compliant 	WHITE ON BLUE	-	-	1805243	1805417	1805423	
	WHITE ON PURPLE	-	-	1805415	1805421	1805428	
	WHITE ON BROWN	-	-	1805412	1805418	1805424	
PERMANENT POLYESTER Length 18' 5.5m - UL Recognized Component to UL969 - RoHS compliant 	BLACK ON WHITE	1805442	18482	18483	18484	1734523	
	BLACK ON CLEAR	1805440	18508DMO	622289	622290	1805433	
	BLACK ON METALLIC	1805441	18485	18486	18487	1805434	
HEAT-SHRINK TUBE Length 5' 1.5m - UL Recognized Component to UL224 - Meets MIL-STD-202G, MIL-M-81531 & SAE-DTL 23053/5 (Class 1 & 3) - RoHS compliant 	BLACK ON WHITE	18051	18053	18055	18057	1805443	
	BLACK ON YELLOW	18052	18054	18056	18058	1805444	
FLEXIBLE NYLON Length 11.5' 3.5m - UL Recognized Component to UL969 - RoHS compliant 	BLACK ON WHITE	-	-	18488	18489	1734524	
	BLACK ON YELLOW	-	-	18490	18491	1734525	
SELF-LAMINATING Length 18' 5.5m - RoHS compliant 	BLACK ON WHITE	-	-	-	-	1734821	